



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SRW12US

SmartRack 12U Wall Mount Rack Enclosure Cabinet



Highlights

- 12U with adjustable front and rear vertical rackmount rails
- Hinged cabinet swings away from wall bracket for easy equipment access (swing direction is reversible)
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation

Description

The SRW12US 12U Wall Mount Rack Enclosure Cabinet is designed to integrate wall-mounting, easy equipment access, and cable management in IT network applications with limited floor space. Ventilated front door and side panels allow generous airflow to keep equipment operating safely. Adjustable rack rails with square mounting holes accommodate up to 12U of standard 19" rackmount equipment. Supports up to 140 lbs of equipment. A sturdy hinge between the cabinet and the wall-mount bracket allows the cabinet to swing away from the wall for easy access to equipment and cabling. Top and bottom panels include convenient cutouts for cable routing.

Features

- 12U wall-mounted enclosure
- Adjustable mounting depths from 3" to 20.5" inches
- Ventilated front door and side panels for increased airflow
- Hinged cabinet swings away from wall bracket for easy equipment and cable access
- Locking, reversible front door
- Locking, removable side panels
- Top and bottom panel cable access openings
- Fully assembled for quick installation
- 5 year warranty

Specifications

PHYSICAL	
Shipping weight (lbs)	70
Shipping weight (kg)	31.5
Unit Dimensions (cm)	EXTERNAL DIMENSIONS: 63.5 x 60 x 54.9 (HWD)
Unit Dimensions (in)	EXTERNAL DIMENSIONS: 25 x 23.63 x 21.6 (HWD)

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Patch Panels	N252-012	12-Port Cat6 Patch Panel 568B	-
Patch Panels	N252-024	24-Port Cat6 Patch Panel 568B	-
Patch Panels	N252-048	48-Port Cat6 Patch Panel 568B	-
Rack Accessories	SR1UPANEL10	1U Blanking Panel Kit (10 pieces; toolless mounting.)	-
Rack Accessories	SR1UPANEL50	1U Blanking Panel Kit (50 pieces; toolless mounting.)	-
Rack Accessories	SRCABLEDUCT1U	1U Horizontal Cable Manager (Finger duct with cover.)	-
Rack Accessories	SRCABLERING1U	1U Horizontal Cable Manager (Flexible ring type.)	-
Rack Accessories	SRCABLERING2U	2U Horizontal Cable Manager (Flexible ring type.)	-
Rack Accessories	SRCAGENUTS	Threaded Hole Hardware Kit (Includes 50 M6 screws and washers.)	-
Rack Accessories	SRCASTER	Heavy-Duty Rolling Caster Kit (Includes 4 casters. Casters are included with 48/42/25U enclosures.)	-
Rack Accessories	SRFAN3U	3U Fan Panel, 120V (3 high-performance fans; 210 CFM; 5-15P plug.)	-
Rack Accessories	SRSWITCH	Magnetic Door Switch Kit (2-pack for front and rear doors; requires ENVIROSENSE.)	-
Rack Accessories	SRXFAN3U	3U Fan Panel, 230V (3 high-performance fans; 210 CFM; C14 inlet.)	-
Rack Accessories	UPSHDEARKIT	Heavy-Duty Mounting Ear Kit (Supports 2U cabinets up to 65 lb / 29 kg from front vertical rails in 4-post racks and enclosures. Not suitable for 2-post mounting.)	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4266.