# **Quick Start Guide**

# HDMI to VGA Adapter with Audio

Model: P131-000-A-DISP

Este guía esta disponible en español en la página de Tripp Lite: www.tripplite.com/support

Ce guide est disponible en français sur le site Web de Tripp Lite : www.tripplite.com/support

Русскоязычная версия настоящего краткого руководства представлена на веб-сайте компании Tripp Lite по адресу: www.tripplite.com

#### PROTECT YOUR INVESTMENT!

Register your product for quicker service and ultimate peace of mind. You could also win an ISOBARGULTRA surge protector—a \$100 value!

www.tripplite.com/warranty





1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support

Copyright © 2018 Tripp Lite. All rights reserved.

#### **Product Features**

- · Connect your HDMI-enabled device to a VGA display with audio
- Supports resolutions up to 1920 x 1200 @ 60 Hz
- Bus-powered HDMI connection (USB Micro-B port included on unit in the event additional power is needed)
- HDCP 1.4 and HDMI 1.4b compliant
- · Plug-and-Play—no software or drivers to install

# Package Includes

- HDMI to VGA Adapter with Audio
- USB Micro-B to USB-A Cable (1 ft.)
- 3.5 mm Stereo Audio Cable (1 ft.)
- · Owner's Manual

#### Installation

Note: Make sure all devices you are connecting are powered off prior to installation.

- Connect an HDMI cable between the HDMI port on the adapter unit and an HDMI source.
- 2. Connect the VGA male end of the adapter unit to the VGA display.
- **3.** Connect a 3.5 mm audio cable between the 3.5 mm port on the unit and the audio jack on your monitor or speakers.
- 4. Turn on the power to the connected devices. If you are not receiving a signal after powering up, connect a USB cable between the Micro-B port on the unit and the USB-A port on a USB charger or the HDMI source.

### **Specifications**

Connectors	
Audio/Video Input	HD15 (Male)
Video Output	HDMI (Female)
Audio Output	3.5 mm (Female)
USB (Power)	USB Micro-B (Female)
Environmental	
Operating Temperature	32 to 104 °F (0 to 40 °C)
Storage Temperature	-4 to 140 °F (-20 to 60 °C)
Relative Humidity	10% to 90%, Non-Condensing

## **Warranty and Product Registration**

#### 3-YEAR LIMITED WARRANTY

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of three (3) years from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment, which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Some states do not permit limitation or exclusion of implied warranties: therefore, the aforesaid

limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT,

SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS

PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP

LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use
of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or

otherwise.

### **Warranty and Product Registration**

#### PRODUCT REGISTRATION

Visit www.tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!\*

\* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

#### FCC Notice, Class B

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- · Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- · Consult the dealer or an experienced radio/TV technician for help.

Any changes or modifications to this equipment not expressly approved by Tripp Lite could void the user's authority to operate this equipment.

Use of this equipment in life support applications where failure of this equipment can reasonably be expected to cause the failure of the life support equipment or to significantly affect its safety or effectiveness is not recommended.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.





1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support

18-11-093 93-387B RevB