



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SU6000RT4U

SmartOnline 6kVA On-Line Double-Conversion UPS, 4U Rack/Tower, 208/120V or 240/120V NEMA outlets, Split-phase input

Highlights

- 6000VA / 6kVA / 4200W on-line double-conversion UPS
- 208/120V or 240/120V +/-3% output at 60Hz
- 4U Rack/Tower compatible; Hot-swappable power and battery modules
- USB, RS232 & EPO ports; support for SNMP/WEB card options
- Front panel LEDs with detailed LCD monitoring and control screen
- Expandable runtime with optional external battery packs
- NEMA L14-30P input (4 wire split phase); L6-30R, L6-20R & 5-15/20R outlets



Description

Tripp Lite 6kVA SmartOnline Hot-Swappable Modular Rack/Tower UPS. 6000VA on-line, double-conversion UPS for server, network and telecommunications equipment. Maintains battery-derived AC output during blackouts with active, full-time power conditioning. Fault-tolerant auto-bypass prevents unexpected service interruptions during overload or internal fault conditions. Single all-in-one housing installs in 4 rack spaces (4U). Upright tower installation with optional 2-9USTAND accessory. 2 post rackmount installation with optional 2POSTRMKITWM. Full-time sine wave output within 3% of selectable 208/120 or 240/120V AC. Corrects brownouts and overvoltages from 65V to 140V (L-N). Expandable runtime with optional external battery packs. Converts raw input from AC to DC, then back to perfect sine wave AC output with enhanced protection from harmonic distortion, fast electrical impulses and other hard-to-solve power problems not addressed by other UPS types. Highly efficient operation in optional economy mode setting, saving BTU heat output and energy costs. Network-grade AC surge and noise suppression. Network management interfaces include combination RS-232 enabled and contact closure serial port, enhanced USB port and SNMPWEBCARD slot. Includes USB and DB9 serial ports. Built-in DB9 port offers both enhanced RS-232 enabled monitoring data, plus contact closure monitoring ability. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces. Includes PowerAlert monitoring software and complete cabling. Emergency Power Off (EPO) interface. Front panel LEDs and LCD readout with scroll controls support visual monitoring of all major UPS functions. LED/LCD display panel easily rotates for viewing in rackmount or tower configurations. Audible alarm. Self test. 4-post rackmount accessories. L14-30P split phase 4 wire plug-in connection: two L6-30R, two L6-20R and eight 5-15/20R output receptacles. Input cord and outlets are mounted on a detachable backplate with manual bypass switch to enable hot-swappable UPS replacement without powering off connected equipment. Optional SUPDM56HW installable backplate accessory enables hardwire input-output connections. Optional external Power Distribution Unit (PDU) options available. Internal batteries and optional external battery packs are field replaceable and hot swappable. Attractive all-black color scheme. \$250,000 [connected equipment insurance](#);

Package Includes

- SU6000RT4U UPS System (with SUPDM56 detachable PDU module)
- USB, DB9 and EPO cabling
- Rackmount installation kit for 4 post rack enclosures
- Owner's manual and warranty information

Features

- True online, double-conversion UPS provides pure, full-time sine wave AC output free of surges, voltage fluctuations and line noise
- 6000VA/4200 watt output power capacity with dual voltage output of 208/120 or 240/120V
- 4U all-in-one high power density housing supports rackmount installation in only 4 rack spaces
- Dual conversion UPS actively converts raw input from AC to DC, then back to perfect sine wave AC output with enhanced protection from harmonic distortion, fast electrical impulses and other hard-to-solve power problems not addressed by other UPS types
- Input cord and outlets are mounted on a detachable backplate with manual bypass switch to enable hot-swappable UPS replacement without powering off connected equipment
- Optional SUPDM56HW and SUPDMB568HW installable backplate accessories enable hardwire input-output connections
- Provides perfectly regulated, sine wave output power free of line noise, transient surges and frequency variation for the most efficient operation of critical servers, networking and telecommunications equipment
- Maintains output within 3% of selected 208/120 or 240/120V nominal voltage during brownouts and overvoltages
- Supports connected equipment during blackouts for 20/8 minutes at half/full load levels, runtime is further expandable with optional external battery packs
- Some external battery configurations require the use of Tripp Lite's [External Battery Configuration Software](#) (see manual)
- Network interfaces support simultaneous communications via DB9 port, USB port and SNMPWEBCARD slot
- Included PowerAlert UPS monitoring software supports safe unattended shutdown, monitoring and control via local connected servers, plus any number of additional servers over IP
- Communications ports support on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current monitoring, battery charge current, battery capacity, AC line frequency, timed inverter shutoff, activate self-test and output power control
- Includes USB and DB9 serial ports. Built-in DB9 port offers both enhanced RS-232 enabled monitoring data, plus contact closure monitoring ability. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X.
- Built-in Emergency Power Off (EPO) interface with cable
- Includes 12 built-in output receptacles (2 L6-30R, 2 L6-20R, 8 NEMA 5-15/20R)
- L14-30P split phase, 4 wire plug-in connection (featured on included detachable PDU). Optional SUPDM56HW hardwire input/output PDU available separately
- Front panel LEDs and LCD readout with scroll button enables visual confirmation of all major UPS functions and current site electrical conditions
- Front panel switches enable power on/off control, self-test and alarm cancel functions
- Included adjustable mounting rails support installation in 4 post 19 inch rack enclosures
- Optional 2-9USTAND set of tower stands supports upright tower installation
- Optional 2POSTRMKITWM accessory enables 2 post rackmount installation
- UPS ships fully assembled in full compliance with DOT regulations, no time consuming connection of internal batteries by user is required
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Detachable PDU with built-in manual bypass switch enables hot-swappable UPS replacement without powering off connected equipment
- \$250,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	6000
Output kVA capacity (kVA)	6
Output Watt Capacity (watts)	4200
Output kW capacity	4.2
Output power factor	0.7
Output Capacity Details	6,000 VA (240V) / 5400 VA (208V) / 4200 watts (208/240V)
Crest Factor	3:1
Nominal Output Voltage(s) Supported	120V; 208V; 240V

Nominal Voltage details	240/120 or 208/120 split phase output
Frequency compatibility	60 Hz
Output voltage regulation (line mode)	+/- 3%
Output voltage regulation (Economy line mode)	+/- 10%
Output voltage regulation (Battery mode)	+/- 3%
Built-in UPS output receptacles	8 5-15/20R outlet(s); 2 L6-20R outlet(s); 2 L6-30R outlet(s)
Output circuit breaker	20A branch rated breakers (x4) protect 2 5-15/20R outlets each, 20A double pole breakers (x2) protect one L6-20R each, L6-30R outlets are unbreakered
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	Pure Sine wave
INPUT	
Rated input current (at maximum load)	24A
Nominal Input Voltage(s) Supported	208V AC / 120V AC (4 wire split single phase); 240V AC /120V AC (4 wire split single phase)
UPS input connection type	L14-30P
UPS input connection description	4 wire split-phase input (L1, L2, N, G)
UPS Input cord length (ft.)	10
UPS Input cord length (m)	3
Recommended Electrical Service	30A 208/120V Split Phase
Input cord length (m)	3
BATTERY	
Full load runtime (minutes)	8 min. (4200w)
Half load runtime (minutes)	20 min. (2100w)
Expandable battery runtime	Supports extended runtime with optional external battery packs

External battery pack compatibility	BP192V12-3U; BP192V557C-1PH; BP192V787C-1PH; BP192V1037C-1PH; BP192V1407C-1PH
DC system voltage (VDC)	192
Battery recharge rate (included batteries)	Less than 6 hours from 10% to 80%
Replacement battery cartridge (internal UPS battery replacement)	RBC9-192
Battery Access	Front panel battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Online, double-conversion power conditioning
Overvoltage correction	3% output voltage regulation during overvoltages to 140 (measured L1-N : L2-N)
Undervoltage correction	2% output voltage regulation during undervoltages to 65 (measured L1-N : L2-N)
LEDS ALARMS & SWITCHES	
LED Indicators	6 LEDs indicate line power, online mode, economy/bypass mode, on-battery, charger and AC output status; LCD screen offers additional information and control options
Alarms	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
Alarm cancel operation	Alarm cancel switch
Switches	Includes main power off/on switch, plus 2 switches to set and execute scrollable LCD functions. A manual bypass switch featured on the detachable PDU allows for complete removal of the UPS during routine maintenance without disrupting power to connected loads. Battery Charge level switch allows the charger output to be adjusted to a higher charge rate when external battery packs are added.
SURGE / NOISE SUPPRESSION	
UPS AC suppression response time	Instantaneous
EMI / RFI AC noise suppression	Yes
AC suppression response time	Instantaneous
PHYSICAL	
Installation form factors supported with included accessories	4 post 19 inch rackmount (mounting rail kit included)
Installation form factors supported with optional accessories	2 post rackmount (2POSTRMKITWM); Tower (2-9USTAND)
Primary form factor	Rackmount

UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	7 x 17.5 x 30.8
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	17.8 x 44.4 x 78.1
Installed whole system maximum rack depth (inches)	30.8
Installed whole system maximum rack depth (cm)	78.1
Installed whole system total rack space height (rack spaces)	4U
Secondary form factor	Tower (requires 2-9U STAND)
UPS / Power Module weight (lbs)	149.6
UPS / Power Module weight (kg)	67.9
UPS dimensions details	4U UPS with internal batteries
UPS Shipping dimensions (height x width x depth / inches)	13.2 x 37 x 23
UPS Shipping dimensions (height x width x depth / cm)	33.7 x 94 x 58.4
Shipping weight (lbs)	189.2
Shipping weight (kg)	85.9
UPS housing material	Steel
Cooling method	Fan
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius.
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius.
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	1586.7
Battery mode BTU / hr. (full load)	1412.3

Operating Elevation (ft)	0-3000m (0 to 10,000 ft.)
Audible Noise	60 dBA at front side 1 meter
Operating Elevation (m)	0-3000 m
COMMUNICATIONS	
Communications interface	USB (HID enabled); DB9 Serial; Contact closure; EPO (emergency power off); Slot for SNMP/Web interface
Network monitoring port description	RS232 and contact closure communications are supported on one DB9 port
PowerAlert software	Included
Communications cable	USB and DB9 cabling included
LINE / BATTERY TRANSFER	
Transfer time	No transfer time (0 ms.) in online, double-conversion mode
Low voltage transfer to battery power (setpoint)	65V (L1-N:L2-N)
High voltage transfer to battery power (setpoint)	140V (L1-N:L2-N)
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Automatic inverter bypass; Manual bypass switch; Detachable hot-swap PDU; Hot swappable UPS power module; Hot swappable batteries
Green & high efficiency features	High efficiency economy mode operation; Schedulable daily hours of economy mode operation
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Extended Warranties	WEXT3-SU6000	3-Year Extended Warranty - For SU6000 models	1
Extended Warranties	WEXT5-SU6000	5-Year Extended Warranty - For SU6000 models	1
External Battery Packs	BP192V1037C-1PH	External battery pack for use with select Tripp Lite UPS Systems	1

External Battery Packs	BP192V12-3U	BP192V12-3U - External Battery Pack for UPS System	1
External Battery Packs	BP192V1407C-1PH	External battery pack for use with select Tripp Lite UPS Systems	1
External Battery Packs	BP192V557C-1PH	External battery pack for use with select Tripp Lite UPS Systems	1
External Battery Packs	BP192V787C-1PH	External battery pack for use with select Tripp Lite UPS Systems	1
Hardwire Accessory Modules	SUPDM56HW	SUPDM56HW - UPS Accessory - Hardwire PDU Module	1
Hardwire Accessory Modules	SUPDMB568HW	SUPDMB568HW - UPS Accessory - Hardwire PDU Module	1
Rackmount/Wallmount Kits	2POSTRMKITHD	Enables 2-Post Rackmount Installation of 3U and Larger UPS, Transformer and Battery Pack Components	1
Shutdown Cable Kits	AS400CABLE KIT	Power Management Tools - UPS Communication Cable Kit for System i / AS400 / iSeries Servers	1
SNMP Accessories	ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
SNMP Accessories	SNMPWEBCARD	For remote monitoring and control via SNMP, Web, or Telnet.	1
Surge Protectors	DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	1
Surge Protectors	DNET1	Network Surge Suppressor - Essential protection for data and communication lines	1
Surge Protectors	DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	1
Tower Stands	2-9USTAND	Enables Tower Placement of Rackmount UPS Systems	1
UPS Accessories	MODBUSCARD	For remote monitoring and control via MODBUS protocol	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3184.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.