

## SmartOnline 120/208V 3-Phase Wye 60kVA Modular 3-Phase UPS System, On-line Double- Conversion UPS for North America

MODEL NUMBER: **SU60K**



### Description

Tripp Lite's SU60K (60kVA) SmartOnline Modular 3-Phase Intelligent, True On-Line UPS System provides 100% system availability with N+1 modular architecture and 1+1 parallel capability. In an N+1 configuration, the SU60K features three self-contained, redundant 20kVA power modules that can be hot-swapped (with the load powered) if maintenance is required. Connect two SU60K models in parallel (1+1 configuration) to provide fail-safe redundancy (two 60kVA models supporting a 60kVA load) or to increase capacity (two 60kVA models supporting an 120kVA load).

The SU60K provides mission-critical equipment with the highest level of power protection available. Large capacity 60,000VA/48,000 watt UPS continually converts incoming AC power into filtered DC power, and then resynthesizes it back into AC power with a pure sine wave. Perfectly regulated, continuous sine wave output with zero transfer time offers compatibility with all equipment types. The SU60K's high input power factor, advanced IGBT inverter technology and Digital Signal Processor (DSP) technology create less than 3% input Total Harmonic Distortion (THDi). With SU60K's low THDi, generators run cooler and last longer, allowing managers to save installation costs by installing a generator with a capacity equal to their equipment load (a 1:1 ratio). Extremely efficient operation (up to 96%) saves money by lowering electricity consumption. Hardwire input and output connections. SU60K features 120/208V AC, 3-phase, 4-wire (plus ground), wye input and output. It also features a wide input voltage correction range: 94-150/163-260V AC. Frequency is 50 or 60 Hz (auto-selectable). SU60K features a single small-footprint tower power module. A stand-alone hardwired external battery module (Models BP480V26B or BP480V40C with matching battery cabinets, available separately) is required for operation and to provide battery backup support. Additional external BP480V26B or BP480V40C battery modules can be connected for extended runtime. Additional battery cabinets for extended runtime solutions also available; contact Tripp Lite for more information. A manual bypass breaker as well as an automatic bypass function ensure 100% availability of connected equipment by safely passing through AC power if the UPS requires maintenance. A built-in RS-232 communication port works with PowerAlert Software to provide shutdown commands

### Highlights

- 60,000 VA (60kVA) tower UPS with 3 hot-swappable power modules
- N+1 redundant modular architecture helps ensure 100% availability
- 1+1 parallel capability allows for system redundancy or increased capacity
- Low THDi saves installation costs by allowing 1:1 generator sizing
- 3-phase hardwire (120/208VAC) input/output. Wide input voltage correction range (94-150VAC/163-260VAC)
- On-line, double-conversion operation with zero transfer time; IGBT technology; extremely efficient operation (up to 96%)
- Runtime is expandable via external battery cabinet options

### Package Includes

- SU60K UPS System
- Serial communications cable
- Parallel cable (for 1+1 operation)
- Instruction manual and startup checklist
- Warranty information



Powering Business Worldwide



and condition reporting. An accessory slot accepts an optional network management card option. Front panel combination LCD/LED display alerts users to a variety of UPS operational modes and conditions. The LCD display includes a real-time event log screen with up to 500 events listed. A dynamic battery management screen optimizes battery function to lengthen service life and allows cold restart of UPS during a prolonged blackout to utilize its batteries for periodic system access or data retrieval. An Emergency Power Off button turns UPS output OFF and disables Bypass output. Built-in Emergency Power Off (EPO) dry-contact interface supports remote emergency shutdown in large facilities. A start-up service program is recommended to enhance the reliability of the installation.

## Features

- N+1 configuration: three self-contained, redundant 20kVA power modules can be hot-swapped (with the load powered) if maintenance is required
- 1+1 configuration: connect two SU60K models in parallel to provide fail-safe redundancy or to increase capacity
- High input power factor, advanced IGBT inverter technology and Digital Signal Processor (DSP) technology create low input Total Harmonic Distortion (THDi)
- Extremely efficient operation (up to 96%) saves money by lowering electricity consumption
- True on-line, double conversion UPS with IGBT technology provides pure, sine wave AC output at all times
- Maintains continuous operation through blackouts, voltage fluctuations and surges with zero transfer time
- Removes harmonic distortion, electrical impulses, frequency variations and other hard-to-solve power problems
- 60,000VA/48,000W power capacity with 3-phase, hardwire 120/208VAC input/output connections
- Features a wide input voltage correction range: 94-150/163-260VAC
- Precision +/-1% output voltage regulation
- A stand-alone hardwired external battery module (Models BP480V26B and BP480V40C, available separately from Tripp Lite) is required for operation and to provide battery backup support. Additional external battery modules can be connected for extended runtime.
- Front panel combination LCD/LED display includes a real-time event log screen with up to 500 events listed
- Dynamic battery management screen optimizes battery function to lengthen service life and allows cold restart of UPS
- Serial port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [triplite.eaton.com/products/power-alert](http://triplite.eaton.com/products/power-alert)
- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX, SNMPWEBCARD and MODBUSCARD
- Emergency Power Off button turns UPS output OFF and disables Bypass output
- Built-in Emergency Power Off (EPO) dry-contact interface supports remote emergency shutdown in large facilities
- Start-up service program is recommended to enhance the reliability of the installation

## Specifications

OVERVIEW	
UPC Code	037332141323
UPS Type	On-Line



Powering Business Worldwide



INPUT	
Input Phase	3-Phase
Rated input current (Maximum Load)	125A (per phase, online)
Nominal Input Voltage(s) Supported	120/208V 3-PH Wye
Nominal Input Voltage Description	3-Phase Wye, 4 wire (L1, L2, L3, N, G)
UPS Input Connection Type	Hardwire
OUTPUT	
Output Capacity (VA)	60000
Output Capacity (kVA)	60
Output Capacity (Watts)	48000
Output Capacity (kW)	48
Power Factor	0.8
Crest Factor	3:1
Frequency Compatibility	50 / 60 Hz
Output Voltage Regulation (Line Mode)	+/- 1%
Output Voltage Regulation (Battery Mode)	+/- 1%
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120/208V 3-PH Wye
Output Receptacles	Hardwire
Individually Controllable Load Banks	No
BATTERY	
Expandable Runtime	Yes
Expandable Runtime Description	External battery pack wiring is contractor supplied
External Battery Pack Compatibility	BP480V200; BP480V26B; BP480V300; BP480V400; &nbsp;<a class="productLink" href="//tripplite.eaton.com/External-Battery-Pack-for-select-Tripp-Lite-3-Phase-UPS-Systems~BP480V40C">BP480V40C</a>&nbsp;<a class="productLink" href="//tripplite.eaton.com/External-Battery-Pack-3-Phase-UPS-Systems~BP480V500">BP480V500</a>&nbsp;
DC System Voltage (VDC)	+/- 240VDC
Battery Recharge Rate (Included Batteries)	Less than 4 hours from 10% to 90%
Battery Replacement Description	Hot-swappable, replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning

Overvoltage Correction	Maintains continuous operation without using battery power during overvoltages to 150 / 260 (3-Phase, 4-Wire, wye), reducing output within 1% of nominal
Undervoltage Correction	Maintains continuous operation without using battery power during brownout / undervoltage conditions to 94 / 163 (3-Phase, 4-Wire, wye)
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	ON button turns UPS's inverter ON. OFF button turns UPS's inverter OFF. LCD Display Control Buttons browses through and selects items displayed on LCD screen. Emergency Power Off button turns UPS output OFF and disables Bypass output. Manual Bypass breaker bypasses the UPS's inverter during maintenance.
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Audible Alarm	Alarms warn against a variety of operational conditions: low-battery, overload, shutdown, bypass and more
LED Indicators	4-LED Display: Displays normal AC input, on battery power, bypass input and fault conditions
<b>SURGE / NOISE SUPPRESSION</b>	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	4675
AC Suppression Response Time	Instantaneous
<b>PHYSICAL</b>	
Primary Form Factor	Tower
Cooling Method	Fans
Installation Form Factors Supported with Included Accessories	Tower
Primary UPS Depth (mm)	958
Primary UPS Height (mm)	1,699
Primary UPS Width (mm)	521
Shipping Dimensions (hwd / in.)	75.00 x 28.50 x 45.00
Shipping Dimensions (hwd / cm)	190.50 x 72.39 x 114.30
Shipping Weight (lbs.)	1356.00
Shipping Weight (kg)	615.07
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	169.93 x 52.07 x 95.76
UPS Power Module Dimensions (hwd, in.)	66.9 x 20.5 x 37.7
UPS Power Module Weight (kg)	534.11
UPS Power Module Weight (lbs.)	1177.5
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius



Powering Business Worldwide



Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	13998
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	14254
<b>COMMUNICATIONS</b>	
Network Management Cards	SNMPWEBCARD; &nbsp;<a class="productLink" href="//tripplite.eaton.com/Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems~TLNETCARD">TLNETCARD</a>&nbsp;; WEBCARDLX; &nbsp;<a class="productLink" href="//tripplite.eaton.com/MODBUS-Management-Accessory-Card-UPS-Remote-Monitoring-Control~MODBUSCARD">MODBUSCARD</a>&nbsp;
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at <a href="https://tripplite.eaton.com/products/power-alert">https://tripplite.eaton.com/products/power-alert</a>
Communications Cable	DB9 cabling included
Communications Interface	DB9 Serial; Slot for SNMP/Web interface
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Low Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation during undervoltages as low as 94 / 163V AC (3-Phase, 4-Wire, wye). Below this point, output is maintained utilizing battery reserves.
High Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation during overvoltages as high as 150 / 260V AC (3-Phase, 4-Wire, wye). Above this point, output is maintained utilizing battery reserves.
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Hot swappable batteries; Auto Probe Monitoring (requires WEBCARDLX); Zero transfer time; On-Line/Double-Conversion
Green Energy-Saving Features	High efficiency economy mode operation; Schedulable daily hours of economy mode operation
<b>APPLICATIONS</b>	
UPS Applications	Mission Critical Applications
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty
3-Phase Warranty Statement	<a href="#">Tripp Lite 3-Phase UPS Factory Warranty</a>



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.