


TAA-Compliant Protect It! 7-Outlet Surge Protector, 7 ft. (2.13 m) Cord, 2450 Joules, Black Housing

MODEL NUMBER: **SUPER7BTAA**



Highlights

- Compliant with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases
- 7 outlets/7-ft. (2.13 m) cord
- 2450 joule rating

Package Includes

- SUPER7BTAA Surge Suppressor
- Instruction manual with warranty information

Description

Tripp Lite's Super7BTAA is compliant with the Federal Trade Agreement Act (TAA) for GSA schedule purchases. The SUPER7B Surge Suppressor from Tripp Lite has 7 outlets, a 7-ft. (2.13 m) cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2450 joules to handle the strongest surges. \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- Compliant with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases
- 7 outlets
- 7-ft. (2.13 m) cord with space-saving right-angle plug
- Surge suppression rating: 2450 joules
- Child Safety Covers
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required
- EMI/RFI noise filtering
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting

Specifications

OVERVIEW	
UPC Code	037332183422
INPUT	



Powering Business Worldwide



Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	7
Right-Angle Plug	Yes
Input Cord Length (m)	2.13
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2450
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	400 L-G, 400 L-N, 400 N-G
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No



Powering Business Worldwide



PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Shipping Dimensions (hwd / cm)	0.00 x 0.00 x 0.00
Shipping Weight (lbs.)	0.00
Shipping Weight (kg)	0.00
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	5.1 x 6.2 x 33.7
Unit Weight (lbs.)	1.2
Unit Weight (kg)	0.54
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL 1449; CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.