

SmartRack 8U/12U/22U Expandable Very Low-Profile Patch-Depth Wall-Mount 2-Post Open-Frame Rack

MODEL NUMBER: SRWO8U22MD



Expandable rack storage for secure IT areas with limited floor space where easy access to patch panels and network cabling is important, such as network wiring closets and back offices.

Description

The SRWO8U22MD SmartRack 8U/12U/22U Expandable Very Low-Profile Wall-Mount 2-Post Open-Frame Rack is ideal for storing patch panels and other shallow equipment in secure IT areas with limited floor space. Mounted to the wall or resting on the floor, this rack offers fast, easy access to network components and cabling. It's compatible with EIA-standard 19-inch rack equipment that supports two-post mounting and a maximum mounting depth of 11.5 inches.

Constructed from heavy-duty steel in a durable black powder-coated finish, the open-frame rack has a maximum load capacity of 150 lbs (68 kgs). The expandable design allows you to assemble the rack in an 8U, 12U or 22U configuration to meet your current needs, while leaving rack space in reserve for future expansion. It saves precious space and allows IT managers easy access for organizing, installing and servicing equipment and cabling.

The rack is easy to assemble using the included hardware. The vertical mounting rails have threaded 12-24 holes for securing equipment to the steel frame.

Features

Saves Valuable Workspace

- Perfect for installing patch panels and other shallow networking equipment in secure IT areas with limited floor space
- Houses EIA-standard 19 in. rack equipment up to 11.5 in. deep
- Maximum load capacity of 150 lbs (68 kgs)

Open-Frame Design in 3 Configurations

- Assembles in 8U, 12U or 22U to meet current needs
- Expands to add equipment later without buying a bigger rack
- Allows easy access for organizing, installing and servicing equipment and cabling

Easy Assembly and Installation

- Made from heavy-duty steel in a durable black powder-coated finish
- Easy to assemble with included hardware

Highlights

- Maximum load capacity of 150 lbs (68 kgs)
- Secures 19 in. rack equipment up to 11.5 in. deep
- Configures to 8U, 12U or 22U of rack space
- Heavy-duty steel construction designed to last
- Easy to assemble with included hardware

Package Includes

- (24) 12-24 equipment mounting screws
- (16) M5 button-head cap screws
- (8) M6 x 12 Phillips-head screws
- (2) Short vertical mounting rails
- (2) Long vertical mounting rails
- (2) Mounting rail tie plates
- (2) Metal support straps
- (2) Top/bottom panel frames
- (8) Zip ties
- 3 mm L-shaped hex key
- Owner's manual

- Vertical mounting rails with threaded 12-24 holes
- Wall-mounting holes spaced 16 in. apart to accommodate standard wall stud placement

Specifications

OVERVIEW	
UPC Code	037332187413
Device Compatibility	Patch Panel
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	22U
Rack Depth	Shallow
Maximum Device Depth (cm)	29.21
Maximum Device Depth (in.)	11.5
Maximum Device Depth (mm)	292
Maximum Weight Capacity (lbs.)	150
Maximum Weight Capacity (kg)	68
Shipping Dimensions (hwd / in.)	3.35 x 21.46 x 27.75
Shipping Dimensions (hwd / cm)	8.51 x 54.51 x 70.48
Shipping Weight (lbs.)	17.00
Shipping Weight (kg)	7.71
Unit Dimensions (hwd / in.)	0.000 x 20.110 x 12.000
Unit Dimensions (hwd / cm)	45.22 (8U), 63 (12U), 107.45 (22U) x 51.08 x 30.48
Unit Weight (lbs.)	14.8
Unit Weight (kg)	6.71
Unit Weight Details	Weight varies depending on configuration 8U = 10.24lbs, 12U = 11.25lbs, 22U = 14.08lbs
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	



Powering Business Worldwide



Product Warranty Period (Worldwide)	5-year limited warranty
----------------------------------------	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.