



# Protect It! 7-Outlet Surge Protector, 6 ft. (1.83 m) Cord, 1440 Joules, Tel/Modem Protection, Safety Covers

#### MODEL NUMBER: TLP706TELC











#### **Highlights**

- 7 outlets / 6-ft. cord
- 1440 joule rating
- Modem/fax surge protection
- Integrated child safety covers

#### **Package Includes**

- TLP706TELC Surge Suppressor
- 6-ft. (1.83 m) telephone cord
- Instruction manual with warranty information

### Description

The TLP706TELC surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. High-grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dial-up and DSL modem lines, fax machines, cordless phones and more. Integrated child safety covers. TLP706TELC offers seven total outlets, six-foot (1.8-meter) cord with a space-saving right-angle plug and diagnostic LEDs to warn of wiring problems and suppressor damage. Heavy-grade AC suppression rated at 1440 joules shields equipment from surges and line noise. Black suppressor housing with keyhole mounting tabs lets offers convenient protection of desktop computer equipment and accessories.

#### **Features**

- 1440 joules AC surge suppression shields equipment from the strongest surges and line noise
- 7 AC outlets with integrated child safety covers
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless
  phones and more (pair of RJ11 jacks, 1 line, includes 6-ft. (1.83 m) phone cable)
- $\bullet\,$  6-ft. (1.83 m) cord with space-saving right-angle plug
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Black housing with matching black covers suppressor housing with keyhole mounting tabs allow versatile placement options
- UL1449 3rd Edition Rated (400V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$50,000 Ultimate Lifetime connected equipment insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing
  equipment damage and indicating replacement is required





## **Specifications**

OVERVIEW		
UPC Code	037332175205	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Plug Features	Right Angle (90D)	
Input Cord Gauge Type	14 gauge; SJT	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Details	SJT	
Input Cord Length (ft.)	6	
Right-Angle Plug	Yes	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(7) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(4) Yes	
Outlet Orientation	Single row of 7	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Switches	Two position on/off power switch	
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1440	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
UL1449 Let Through Rating	400V	





EMI / RFI Filtering	Up to 20 dB	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection Details	1 line	
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	Yes	
PHYSICAL		
Material of Construction	Plastic	
Power Cord Color	Black	
Housing Color	Black	
Mounting Holes or Slots	No	
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 207 mm	
Outlets Measurement (Center to Center)	Between Standard Outlets = 28.5mm	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	13.78 x 4.63 x 1.77	
Shipping Dimensions (hwd / cm)	35.00 x 11.76 x 4.50	
Shipping Weight (lbs.)	1.50	
Shipping Weight (kg)	0.68	
Unit Dimensions (hwd / in.)	1.380 x 2.160 x 11.690	
Unit Dimensions (hwd / cm)	3.51 x 5.49 x 29.69	
Unit Weight (lbs.)	1.2	
Unit Weight (kg)	0.54	
Input Cord Color	Black	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed	
Product Compliance	FCC Part 68; RoHS	
WARRANTY & SUPPORT		





Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.