

HDMI over Cat5/6 Passive Extender, Low-Profile Remote Receiver for Video/Audio, Up to 100 ft. (30 m), TAA

MODEL NUMBER: **B126-1P0-MINI**



Works with Tripp Lite's B126-Series transmitters to extend an HDMI signal via one Cat5e/6 cable up to 100 ft. to a projector, monitor or television. Recommended for digital signs, classrooms and trade show presentations.

Description

The B126-1P0-MINI HDMI over Cat5/Cat6 Passive Extender, Low-Profile Remote Receiver works with B126-002 and B126-004 transmitters (sold separately) to extend an HDMI signal to multiple projectors, monitors or televisions in a chain. It's recommended for digital signage, trade shows, presentations, classrooms, churches, retail settings and other applications where the video source is located farther than conventional cables allow.

The compact, low-profile design helps hide the unit from view. The B126-1P0-MINI's built-in HDMI male connector plugs directly into the monitor. The unit can extend a 1080i (@ 60 Hz) signal up to 100 feet (30.5 meters) or a 1080p (@ 60 Hz) signal up to 50 feet (15.2 meters) with a single Cat5e/6 cable. For best results, use 24 AWG solid-wire Cat5e/6 cable (N202-Series) between this unit and the transmitter. In addition to crystal-clear video, the B126-1P0-MINI delivers full, rich stereo and 7.1-channel surround sound (multi-channel or PCM) audio when paired with a B126-002 or B126-004 transmitter. Supports 24-bit True Color (8 bits per channel) and HDCP compatibility. Easy to set up with no software, drivers or external power supply required.

Features

Extends High-Definition Signals

- Works in tandem with B126-002 and B126-004 transmitter units (sold separately)
- Extends a 1080i (@ 60 Hz) signal up to 100-ft. (30.5 m)
- Extends a 1080p (@ 60 Hz) signal up to 50-ft. (15.2 m)
- Connects to transmitter with one Cat5e/6 cable
- Built-in HDMI male connector plugs directly into monitor

Supports the Latest Video and Audio Resolutions

- Works with all operating systems and HDMI video sources
- Supports stereo and 7.1-channel surround sound (multi-channel or PCM) when paired with B126-002 or B126-004
- Supports 24-bit True Color (8 bits per channel) and HDCP

Highlights

- Compact, low-profile design hides unit from view
- Supports high-definition video resolutions up to 1080p (@ 60 Hz)
- Supports stereo and 7.1-channel surround sound audio
- Works with all operating systems and HDMI video sources
- Plug-and-play—no software, drivers or external power supply

Package Includes

- B126-1P0-MINI HDMI over Cat5/Cat6 Passive Low-Profile Remote Receiver
- USB Micro-B cable
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Easy to Set Up and Use

- Plug-and-play engineering—no software or drivers necessary
- No external power required; included USB Micro-B cable provides extra power when necessary

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332200402
Product Type	Receiver
Technology	HDMI; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p @ 60Hz)
Max 720P Range (ft)	100
Max 1080P Range (ft)	50
Max 1280 x 720 (720p) Range (ft)	100
Max 1920 x 1080 (1080p) Range (ft)	50
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Range Extension using other Tripp Lite product	175 ft. @ 1080i 125 ft. @ 1080p
Recommended Cabling	N202-Series Cat6 Patch Cable
Other Tripp Lite product used to extend range	B126-110
Max Supported Color Depth	24-bit True Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	100
Maximum Signal Range (m)	30
Maximum Signal Range Details	100 ft @ 1080i 50 ft @ 1080p
AUDIO	
Audio Output	HDMI
Audio Specification	Pass-through audio



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Bus Powered	No
POWER	
Power Source Type	USB
Power Source	Receiver end only (Optional)
Power Over Cable (PoC) Support	No
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	HDMI (MALE); MICRO-USB B (FEMALE)
Connector Plating	Nickel
Daisy-chainable / Cascadable	Yes
Daisy-chainable / Cascadable Details	Requires B126-110
PHYSICAL	
Color	Black
Number of Displays	1
Form Factor/Mounting Options	Pigtail
Shipping Dimensions (hwd / in.)	1.30 x 5.90 x 4.80
Shipping Dimensions (hwd / cm)	3.30 x 14.99 x 12.19
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.03
Unit Weight (kg)	0.01
Housing	Plastic
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0% to 85%, Non-Condensing
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	100



Powering Business Worldwide

TRIPP LITE
SERIES

Max 480P Range (ft)	100
Max 1440 x 900 Range (ft)	100
Max 1080i Range (ft)	100
Max 480i Range (ft)	100
Max 640 x 480 Range (ft)	100
Max 800 x 600 Range (ft)	100
Max 1600 x 1200 Range (ft)	100
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
Built-In Equalizer	No
HDCP Specification	1.4
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.