

## Protect It! Surge Suppressor - 2 Schuko outlets

MODEL NUMBER: DEU2TEL



### Highlights

- 2 Schuko outlets with internal safety covers
- Tel/modem surge protection
- 750 joules protection
- Green LED display indicates protection is present
- Portable design

### Package Includes

- DEU2TEL surge suppressor
- Instruction manual
- 2 meter phone cord

### Description

Tripp Lite's DEU2TEL offers complete AC and phoneline protection for laptop computers, electronic notepads, PDAs and other portable electronic devices. Integrated phone line protection allows you to safeguard tel/modem and AC connections with a single unit. 2 Schuko outlets and diagnostic LED offer surge suppression up to 750 joules. CE approved.

ELECTRICAL: 250V AC, 50Hz

### Features

- 750 joule rating
- 250V AC, 50 Hz
- 2 Schuko outlets protect against surge damage and EMI/RFI interference
- RJ11 fax/modem protection
- Green LED indicates surge protection is present
- Portable, direct plug-in design slips easily into any briefcase or bag
- Internal child safety covers

## Specifications

OVERVIEW	
UPC Code	037332119469
INPUT	
Recommended Electrical Service	230V (220-250V)
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	250
Input Cord Length (ft.)	0
Right-Angle Plug	No



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

Input Cord Length (m)	0.00
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 Hz
Outlet Safety Covers Detail	Internal child safety covers
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Green "protected" LED
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	750
EMI / RFI Filtering	Yes
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
<b>PHYSICAL</b>	
Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	8.25 x 5.50 x 3.25
Shipping Dimensions (hwd / cm)	20.96 x 13.97 x 8.26
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Unit Dimensions (hwd / in.)	3.500 x 3.750 x 3.000
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>WARRANTY &amp; SUPPORT</b>	



Powering Business Worldwide



Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.