

1U rack/console component power center for all audio/video components -Isobar Audio/Video Power Center

MODEL NUMBER: HT810ISOCTR



Description

Tripp Lite's HT810ISOCTR Isobar Audio/Video Power Center provides ultimate protection - 5700 joules - stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio; and longer component life spans. Perfect for large home/business theater installations, high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. 8 AC outlets (1 front/7 rear), 3-line coaxial protection and 1-line tel/modem protection safeguard all audio/video components. 1U rackmount/console design with included hardware and removable console feet. Input Voltage LCD meter displays the "current usage" with dimmer control. Diagnostic LEDs report operational conditions. Metal housing, 10-ft power cord with right angle plug. Includes color-coordinated outlet/plug labels, 6-ft gold coaxial cable and 6-ft phone cable.

Features

- 5700-joule surge suppression rating with EMI/RFI line noise filtering helps components perform at their peak (sharper, crisper video; deeper, fuller audio; and longer component life spans)
- Exclusive Isolated Filter Banks eliminate interference between connected components
- 2 built-in filtering banks (audio and video)
- Metal housing safely withstands the strongest surges
- 8 surge-protected NEMA 5-15R AC outlets (7 rear and 1 front) safeguard all audio/video components
- 3 sets of surge-protected, HD-compatible 2.2 GHz Type F gold coaxial connectors safeguard components on cable, satellite and antenna connections; two 6-ft. gold coaxial cables included
- 1-line tel/modem surge protection safeguards personal video recorders (PVRs) on a single dial-up connection. Built-in splitter (1 jack in/2 jacks out) allows simultaneous connection of two devices sharing a single line; one 6-ft. phone cable included
- 10-ft. power cord with right-angle NEMA 5-15P plug permits convenient placement anywhere within a home/business theater system
- LCD meter displays "current usage" with dimmer control. Alerts user to input voltage levels Diagnostic LEDs report 4 operational conditions (protection, grounding, power, switched status)

Highlights

- 8 AC outlets
- 5700 joules surge suppression rating
- 3-line HD-compatible gold coaxial surge protection (2.2+ GHz bandwidth)
- 1-line tel/modem surge protection with built-in splitter
- LCD meter with dimmer control
- 3 Diagnostic LEDs
- 10 ft. power cord with right-angle plug

Package Includes

- HT810ISOCTR Isobar Audio/Video Power Center
- Two 6-ft gold coaxial cables, one 6-ft. phone cord
- Color-coordinated outlet/plug labels
- Hardware for 1U rackmounting
- Instruction manual with warranty information



Powering Business Worldwide



- 1U rackmount or console installation options; rackmount hardware and removable rubber console feet included
- Lighted power strip with integrated 15A circuit breaker offers power control and overload protection
- Fail-safe thermal fusing acts like an additional circuit breaker, shutting down the unit and connected equipment in the event of a catastrophic surge
- Color-coordinated outlet/plug labels match outlets to component power cords for easy identification
- Audible alarm immediately alerts user to damaged protection circuitry; perfect for installations where LEDs aren't normally viewed
- TUV tested to UL standards 1449, 60950 and 962A

Specifications

OVERVIEW	
UPC Code	037332136473
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	225000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	Yes
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	12
Overload Protection	15A circuit breaker
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Audible Alarm	Audible alarm
Diagnostic LED Details	Input Voltage LCD meter displays "current usage" with dimmer control. Alerts user to input voltage levels



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	5700
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Safe Thermal Fusing	Yes
UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	Yes
Isolated Filter Banks	2
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line (2.2 GHz Bandwidth)
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Color	Black; Silver
Material of Construction	Metal
Power Cord Color	Black
Form Factors Supported	1U rackmount/console installation
Housing Color	Black; Silver
Included Mounting Accessories	1U rackmounting hardware
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	42mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	3.00 x 22.50 x 16.00
Shipping Dimensions (hwd / cm)	7.62 x 57.15 x 40.64
Shipping Weight (lbs.)	6.00
Shipping Weight (kg)	2.72
Unit Dimensions (hwd / in.)	1.750 x 17.500 x 11.750
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 37.47
Unit Weight (lbs.)	5.5
Unit Weight (kg)	2.49

FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.