

## USB 2.0 A to B Cable (M/M), 15 ft. (4.57 m)

MODEL NUMBER: U022-015



Make the connection between a USB device and your computer's USB port. This USB 2.0 A/B Gold Device Cable assures that you get maximum performance from USB 2.0 devices (e.g. printers, external hard drives). It supports fast data transfer rates up to 480 Mbps, and is backward compatible with USB 1.1.

### Description

This gold USB 2.0 A/B device cable meets or exceeds USB 2.0 specifications. Connects a USB device to a USB port on a computer or hub. Backward compatible - can be used with older USB 1.1 applications as well. All USB 2.0 cabling includes superior foil shielding for reliable, error-free data communications. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) make them perfect for multimedia applications. Features gold-plated connectors and gold-plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

### Features

- Meets or exceeds USB 2.0 specifications
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil
- Gold-plated connectors and gold-plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

## Specifications

| OVERVIEW             |                      |
|----------------------|----------------------|
| UPC Code             | 037332122988         |
| Technology           | USB 2.0 (High Speed) |
| Cable Type           | Passive              |
| CONNECTIONS          |                      |
| Side A - Connector 1 | USB A (MALE)         |

### Highlights

- Meets or exceeds USB 2.0 specifications
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices, including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28AWG data lines, and 24AWG power lines.
- Gold-plated connectors provide superior conductivity

### System Requirements

- Any USB device requiring a USB cable
- USB 2.0 performance only when used with USB 2.0 device and USB 2.0 controller

### Package Includes

- 15-ft. (4.57 m) USB 2.0 Gold Cable USB-A to USB-B



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                              |
|-------------------------------------|------------------------------|
| Side B - Connector 1                | USB B (MALE)                 |
| Connector Style                     | Straight                     |
| <b>PHYSICAL</b>                     |                              |
| Cable Jacket Color                  | Black                        |
| Cable Length (ft.)                  | 15                           |
| Cable Length (m)                    | 4.57                         |
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.50           |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.27         |
| Shipping Weight (lbs.)              | 0.34                         |
| Shipping Weight (kg)                | 0.15                         |
| <b>ENVIRONMENTAL</b>                |                              |
| Operating Temperature Range         | 14° to 122°F (-10° to 50°C)  |
| Storage Temperature Range           | 5° to 140°F (-15° to 60°C)   |
| Operating Humidity Range            | 0% to 90% RH, Non-Condensing |
| Storage Humidity Range              | 0% to 90% RH, Non-Condensing |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                              |
| Product Compliance                  | RoHS                         |
| <b>WARRANTY &amp; SUPPORT</b>       |                              |
| Product Warranty Period (Worldwide) | Lifetime limited warranty    |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.