

Power It! 7-Outlet Power Strip, 25 ft. (7.62 m) Cord, Black Housing

MODEL NUMBER: PS725B



Connect up to 7 electrical devices to a single AC wall socket. Ideal for connecting appliances, power tools, lighting and other electrical equipment in your home, office or work site.

Description

The PS725B Power It!™ 7-Outlet Power Strip is a reliable, convenient, cost-effective 120V 1800W power strip that lets you connect up to seven electrical devices to a single AC wall socket. With a 25-ft. (7.62 m) AC power cord with NEMA 5-15P plug that reaches distant outlets and provides flexibility in placing the unit, this multi-outlet power strip is ideal for use with appliances, power tools, lighting and other electrical equipment in homes, offices and work sites.

Your components plug into seven NEMA 5-15R outlets, including one designed to accept bulky transformers without blocking adjacent outlets. Integrated 15-amp circuit breaker protects all outlets against dangerous overloads. Lighted on/off switch provides one-touch control over connected equipment. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the black plastic housing.

Features

7 Outlets Accept Wide Range of Electronic Devices

- 7 NEMA 5-15R AC outlets accept most appliances, power tools, lights and other devices
- Special end outlet designed for bulky transformers without blocking other outlets

Premium Safety Features

- Lighted on/off switch provides one-touch control over connected equipment
- Integrated 15A circuit breaker protects outlets against overloads
- Exceeds IEEE 587 Category A and B specifications

Fits Effortlessly Into Your Home, Office or Work Site

- 25-ft. (7.62 m) AC power cord with NEMA 5-15P plug long enough to reach distant outlets
- Keyhole slots on bottom panel provide convenient wall or desk mounting options
- Black plastic housing designed for long life

Specifications

Highlights

- 7 NEMA 5-15R outlets, including one for bulky transformers
- 15A resettable circuit breaker prevents dangerous overloads
- 25-ft. (7.62 m) AC power cord reaches distant outlets
- Bottom keyhole slots for mounting to wall or desk

Package Includes

- PS725B Power It! 7-Outlet Power Strip, Black Housing
- Owner's manual

OVERVIEW	
UPC Code	037332190567
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	25
Right-Angle Plug	No
Input Cord Length (m)	7.62
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Outlet Orientation	Single row
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Color	Black
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 151mm; Distance between slot height = 24mm



Powering Business Worldwide



Outlets Measurement (Center to Center)	Distance between standard outlets = 1.14 in.; Distance between last standard outlet and transformer outlet = 1.29 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.40 x 6.60 x 13.80
Shipping Dimensions (hwd / cm)	6.10 x 16.76 x 35.05
Shipping Weight (lbs.)	3.30
Shipping Weight (kg)	1.50
Unit Dimensions (hwd / in.)	1.480 x 2.050 x 11.690
Unit Dimensions (hwd / cm)	3.76 x 5.21 x 29.69
Unit Weight (lbs.)	2.97
Unit Weight (kg)	1.35
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico); UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.