



# External 24V 3U Rack/Tower Battery Pack for Select UPS Systems (BP24V70-3U)

MODEL NUMBER: BP24V70-3U





## Highlights

- Extends the runtime of expandable 24V DC UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rack-mount installation; 4-post installation accessories included
- Options for 2-post rack-mount and tower installation available

#### **Package Includes**

- BP24V70-3U external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual

### **Description**

BP24V70-3U rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 24V rack-mount and tower UPS systems. Includes heavy-gauge cabling with high-current DC connector for safe, simple installation. Included daisy-chain connector enables the connection of additional compatible 24V external battery packs to the host UPS. Included mounting accessories support 3U rack-mount installation in 4-post racks. Options for 2-post center-mounting and upright tower installation available.

Compatible with OMNIVS1500XL, OMNIVSINT1500XL, SMART750RMXL2U, SMART750XLA, SU750RTXL2U, SU750XL, SU1000RTXL2UA, SU1000XLA, SUINT1000RTXL2UA and other UPS systems that specify the use of this battery pack.

#### **Features**

- Offers extended-run UPS operation when used in conjunction with compatible 24V DC UPS systems
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- Daisychain connector enables the connection of additional compatible 24V external battery packs to the host UPS
- Included mounting brackets support rack-mount installation in 4-post racks using only 3 rack spaces (3U)
- 2POSTRMKITHD option supports balanced two-point center-mounting in 2-post equipment racks
- 2-9USTAND option enables upright tower placement

## **Specifications**

OVERVIEW		
UPC Code	037332123305	
INPUT		
Input Phase	Single-Phase	





BATTERY			
DC System Voltage (VDC)	24		
UPS Connection	Attached cable with red/black 75 amp male DC connector		
Typical Battery Lifespan	4-6 years typical (North America)		
PHYSICAL			
Material of Construction	Steel		
Rack Height	3U		
External Battery Pack Form Factor	Rack/Tower		
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount		
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a class="productLink" href="//tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems-2POSTRMKITWM">2POSTRMKITWM</a> ); Tower ( <a class="productLink" href="//tripplite.eaton.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a> )		
Minimum Required Rack Depth (cm)	71.12		
Minimum Required Rack Depth (inches)	28		
Shipping Dimensions (hwd / in.)	12.00 x 23.00 x 32.50		
Shipping Dimensions (hwd / cm)	30.48 x 58.42 x 82.55		
Shipping Weight (lbs.)	166.67		
Shipping Weight (kg)	75.60		
Unit Dimensions (hwd / in.)	5.250 x 17.500 x 25.000		
Unit Dimensions (hwd / cm)	13.33 x 44.45 x 63.5		
Unit Weight (lbs.)	138.89		
Unit Weight (kg)	63.00		
STANDARDS & COMPLIANCE			
Product Compliance	RoHS; CE (Europe)		
WARRANTY & SUPPORT			
Product Warranty Period (U.S. & Canada)	2-year limited warranty		
Product Warranty Period (International)	1-year limited warranty		
Product Warranty Period (Mexico)	1-year limited warranty		
Product Warranty Period (Puerto Rico)	1-year limited warranty		





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.