



# Isobar 2-Outlet Surge Protector, Direct Plug-In, 1410 Joules, Diagnostic LEDs, Metal Housing

MODEL NUMBER: ISOBLOK2-0











Premium protection for A/V home theater components and computer peripherals against dangerous power surges, spikes and line noise. Recommended for home theaters and home offices.

#### **Description**

Premium protection for your expensive computer and audio/visual equipment, the ISOBLOK2-0 Isobar® 2-Outlet Surge Protector features a surge protection rating of 1410 joules to defend your sensitive electronics against even the strongest surges and spikes.

The ISOBLOK2-0 features two NEMA 5-15R outlets, perfect for your flat-panel HDTV and Blu-ray<sup>™</sup> player or a pair of computer peripherals, such as a printer and a router. This unit's unique protection system prevents disruptive line noise from causing A/V distortion, computer lock-ups, data errors and similar problems. Large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors remove EMI/RFI interference and prevent system crashes, reboots and performance problems.

Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the ISOBLOK2-0 protects all three, covering two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

Diagnostic LEDs show power, protection and line fault status at a glance. The ISOBLOK2-0 plugs directly into any standard NEMA 5-15R outlet. Optional mounting hardware is included for permanent attachment to the outlet cover, which will prevent the ISOBLOK2-0 from coming loose accidentally.

#### **Features**

#### 1410-Joule Surge Protection for Your Home Theater Electronics and Computer Peripherals

- Protects your components against surges and spikes
- Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- 2 NEMA 5-15R surge-protected outlets

#### **Premium Safety Features**

- Diagnostic LEDs confirm power, protection and ground status at a glance
- Conforms to current UL 1449 3rd Edition safety standards
- Auto shutoff cuts power to outlets when the protection circuit is compromised

#### Fits Effortlessly Into Your Setup

- Plugs directly into standard NEMA 5-15R outlet with no power cord
- Optional hardware included for permanent mounting to outlet cover
- Metal housing designed for long life

### **Highlights**

- 2 NEMA 5-15R surge-protected outlets
- 1410-joule surge protection rating
- Durable metal housing mounts out of sight behind furniture
- LEDs indicate power, protection and line fault status
- Plugs directly into outlet with no power cord

#### **Package Includes**

- ISOBLOK2-0 Isobar 2-Outlet Surge Protector, Metal Housing
- Mounting hardware
- Owner's manual





## **Backed by Ultimate Lifetime Insurance**

• \$10,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

# **Specifications**

OVERVIEW		
UPC Code	037332010155	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Length Details	Direct Plug-In	
Voltage Compatibility (VAC)	120	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	0	
Right-Angle Plug	No	
Input Cord Length (m)	0.00	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(2) 5-15R	
Circuit Breaker (amps)	15	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Diagnostic LED Details	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1410	
AC Suppression Response Time	NM = 0 ns. CM = <1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
AC Suppression Surge Current Rating	48,000 amps	
AC Suppression Components Used	Metal oxide varistors, toroidal balanced chokes and VHF capacitors	
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended overvoltages and catastrophic occurences	





UL1449 Let Through Rating	330V	
EMI / RFI Filtering	40-80 dB	
Isolated Filter Banks	у	
Immunity	Conforms to IEE 587 / ANSI C62.41	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Material of Construction	Metal	
Form Factors Supported	Direct plug-in format with retaining bracket supports wall mounting directly to a standard AC wall socket	
Housing Color	Gray	
Mounting Holes or Slots	No	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	2.50 x 6.00 x 3.90	
Shipping Dimensions (hwd / cm)	6.35 x 15.24 x 9.91	
Shipping Weight (lbs.)	0.80	
Shipping Weight (kg)	0.36	
Unit Dimensions (hwd / in.)	4.000 x 2.500 x 2.500	
Unit Dimensions (hwd / cm)	10.2 x 6.4 x 6.4	
Unit Weight (lbs.)	0.8	
Unit Weight (kg)	0.36	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	NOM (Mexico); UL 1449; UL 1363	
Product Compliance	RoHS	
Froduct Compilance	NOTES .	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.