



# Duplex Singlemode 9/125 Fiber Patch Cable (LC/SC), 30 m (100 ft.)

MODEL NUMBER: N366-30M



Premium singlemode fiber optic cabling transmits fast, clear data signals through your LAN with twice the bandwidth throughput of multimode cable.

#### **Description**

The N366-30M Duplex Singlemode 9/125 Fiber Patch Cable transmits fast, clear data signals through your LAN with a higher bandwidth than multimode cable for up to twice the throughput. Designed for network equipment that requires singlemode fiber optic patch cables, this 30-meter (100-foot) cable has attenuation loss that meets or exceeds current standards.

The N366-30M has 9/125 duplex (zipcord) fiber made from glass, instead of polymer. The sturdy LC and SC male connectors meet stringent insertion loss standards and feature beveled edges on their glass ends for easy insertion into a patch panel or switch. The FDDI- and OFNR-rated PVC jacket is yellow to easily identify it as a singlemode cable.

### **Features**

#### Fast, Clear Data Transmission Through Your LAN

- Twice the bandwidth throughput of multimode cable
- Ideal for network equipment that requires singlemode fiber optic patch cables
- · Attenuation loss meets or exceeds latest industry standards

#### **Superior Construction for Error-Free Signal Transfer**

- 9/125 duplex (zipcord) fiber made from glass
- Sturdy LC and SC male connectors meet stringent insertion loss standards
- · Beveled edge on glass ends for easy plug insertion
- Yellow-colored for identification as singlemode

# **Specifications**

OVERVIEW	
UPC Code	037332156976
Technology	Singlemode

## **Highlights**

- Attenuation loss meets or exceeds latest industry standards
- 9/125 duplex (zipcord) fiber made from glass
- LC and SC male connectors meet insertion loss standards
- FDDI- and OFNR-rated PVC jacket
- Beveled edge on glass ends for easy plug insertion

#### **System Requirements**

 Fiber optic hardware or NIC card requiring singlemode duplex cable with LC/SC connectors

# **Package Includes**

 N366-30M Duplex Singlemode 9/125 Fiber Patch Cable, 30 m





Optical Mode	OS2	
CONNECTIONS		
Side A - Connector 1	LC DUPLEX (MALE)	
Side B - Connector 1	SC DUPLEX (MALE)	
Endface Polish	UPC	
Endladd Folion		
PHYSICAL		
Cable Jacket Color	Yellow	
Connector Color	Blue; Blue; White	
Cable Jacket Material	LSZH	
Cable Jacket Rating	OFNR	
Clad Diameter (microns)	125	
Core Diameter (microns)	9	
Number of Fibers	2	
Cable Length (ft.)	98.4	
Cable Length (m)	30.00	
Cable Length (in.)	1181.1	
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)	
Shipping Dimensions (hwd / in.)	10.50 x 12.00 x 0.50	
Shipping Dimensions (hwd / cm)	26.67 x 30.48 x 1.27	
Shipping Weight (lbs.)	0.54	
Shipping Weight (kg)	0.24	
Fiber Cable Length	30M (98.4 ft)	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	5% to 85% RH, Non-Condensing	
Storage Humidity Range	35% to 65% RH, Non-Condensing	
COMMUNICATIONS		
Network Compatibility	1 Gbps (Gigabit); 10 Gbps; 25 Gbps; 40 Gbps; 100 Gbps; 400 Gbps	
Attenuation @ 1310NM	0.36 dB/km	
Attenuation @ 1550NM	0.22 dB/km	
Insertion Loss	0.30 dB	
FEATURES & SPECIFICATIONS		





Push/Pull Tabs	No	
Breakout	No	
Trunk	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; REACH	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.