

Quick Start Guide

Cisco Compatible 1000Base-SX SFP Transceiver with DDM, MMF, 850nm, 550M, LC

Model: N286-01GSX-MDLC

Product Features

- 1000Base-SX transceiver supports data transfer rates up to 1.25Gbps
- Compliant with SFP Multi-Source Agreement (MSA) and SFF-8472 with duplex LC receptacle
- Supports Digital Diagnostic Monitoring (DDM)
- 550 m transmission distance using 50/125 MMF cabling
- 300 m transmission distance using 62.5/125 MMF cabling
- Cisco switch compatible
- Hot-pluggable

Package Includes

- N286-01GSX-MDLC
- Quick Start Guide

Optional Accessories

- N320-Series Duplex Multimode 62.5/125 LC Fiber Cables
- N520-Series Duplex Multimode 50/125 LC Fiber Cables
- P999-000 Anti-Static Wrist Strap

Installation

Note:

- SFP transceiver modules are static sensitive devices that require proper handling. An Anti-Static ESD Wrist Strap or similar device should always be used when handling a transceiver module.
 - The transceiver module should never be installed with cables already connected. Always remove cables prior to installation to avoid damaging the cable, cable connectors, and/or optical interface.
 - Installing and uninstalling the transceiver module numerous times will shorten its useful lifespan. Do not uninstall and reinstall the module more than is absolutely necessary.
1. Remove the transceiver module from its packaging, leaving the dust plugs inserted in the LC optical bores.
 2. Gently insert the transceiver module into the module socket of your device, pressing on the dust plugs until it locks into place.
 3. Verify that the transceiver module is locked into place by trying to remove it from the module socket without releasing the latch. If it stays in place, it is seated properly. If not, you will need to re-insert it, firmly pressing on the dust plugs until it locks into place.
 4. Once you have verified that the transceiver module is securely locked in place, you can remove the dust plugs from the LC optical bores and connect your cabling.

Note: Save the dust plugs so that they can be used in the event that the transceiver module needs to be uninstalled and reinstalled.

PROTECT YOUR INVESTMENT!

Register your product for quicker service and ultimate peace of mind.

You could also win an ISOBAR6ULTRA surge protector—a \$50 value!

www.tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support

Copyright © 2014 Tripp Lite. All rights reserved.

Specifications

Specification	N286-01GSX-MDLC
Industry Standards	IEEE 802.3z 1000Base-SX
Connector Type	LC Duplex
Maximum Data Transfer Rate	1.25Gbps
Maximum Transmission Distance	300 m using 62.5/125 MMF, 550 m using 50/125 MMF
Wavelength	850 nm
Fiber Operating Mode	Half/Full Duplex
DDM Support	Yes
H x W x D (inches)	0.41 x 0.54 x 2.24
H x W x D (mm)	10.5 x 13.7 x 57
Weight (lbs.)	0.04
Weight (g)	16.8
Operating Temperature	32°F to 158°F (0°C to 70°C)
Storage Temperature	-40°F to 185°F (-40°C to 85°C)
Humidity	5 to 85% RH, Non-Condensing

3-Year Limited Warranty

Seller warrants this product, if used in accordance with all applicable instructions, to be free from original defects in material and workmanship for a period of 3 years from the date of initial purchase. If the product should prove defective in material or workmanship within that period, Seller will repair or replace the product, in its sole discretion. Service under this Warranty can only be obtained by your delivering or shipping the product (with all shipping or delivery charges prepaid) to: Tripp Lite, 1111 W. 35th Street, Chicago, IL 60609 USA. Seller will pay return shipping charges. Visit www.tripplite.com/support before sending any equipment back for repair.

THIS WARRANTY DOES NOT APPLY TO NORMAL WEAR OR TO DAMAGE RESULTING FROM ACCIDENT, MISUSE, ABUSE OR NEGLIGENCE. SELLER MAKES NO EXPRESS WARRANTIES OTHER THAN THE WARRANTY EXPRESSLY SET FORTH HEREIN. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ALL IMPLIED WARRANTIES, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS, ARE LIMITED IN DURATION TO THE WARRANTY PERIOD SET FORTH ABOVE; AND THIS WARRANTY EXPRESSLY EXCLUDES ALL INCIDENTAL AND CONSEQUENTIAL DAMAGES. (Some states do not allow limitations on how long an implied warranty lasts, and some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitations or exclusions may not apply to you. This Warranty gives you specific legal rights, and you may have other rights which vary from jurisdiction to jurisdiction).

WARNING: The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

PRODUCT REGISTRATION

Visit www.tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

FCC Notice, Class A

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense. The user must use shielded cables and connectors with this equipment. Any changes or modifications to this equipment not expressly approved by Tripp Lite could void the user's authority to operate this equipment.

WEEE Compliance Information for Tripp Lite Customers and Recyclers (European Union)



Under the Waste Electrical and Electronic Equipment (WEEE) Directive and implementing regulations, when customers buy new electrical and electronic equipment from Tripp Lite they are entitled to:

- Send old equipment for recycling on a one-for-one, like-for-like basis (this varies depending on the country)
- Send the new equipment back for recycling when this ultimately becomes waste

Tripp Lite follows a policy of continuous improvement. Product specifications are subject to change without notice.



1111 W. 35th Street, Chicago, IL 60609 USA • www.tripplite.com/support