

Owner's Manual

Portable Battery Bank and Wall Charger, USB-A and USB-C™

Model: UPBW-05K0-1A1C

USB Type-C and USB-C are trademarks of USB Implementers Forum

Este manual esta disponible en español en la página
de Tripp Lite: tripplite.com

Ce manuel est disponible en français sur le site Web
de Tripp Lite : tripplite.com

PROTECT YOUR INVESTMENT!

Register your product for quicker service and ultimate peace of mind.

You could also win an ISOBAR6ULTRA surge protector—a \$100 value!

tripplite.com/warranty



1111 W. 35th Street, Chicago, IL 60609 USA • tripplite.com/support

Copyright © 2019 Tripp Lite. All rights reserved.

Product Features

- Charge your phone, tablet or other mobile device from a wall outlet or on the go
- Sleek, low-profile design is perfect for portable use
- USB ports provide up to 5V, 2.4A (AC Power) or 5V, 3A (DC Power)
- 5000mAh capacity charges devices at maximum power draw for hours
- Four LED battery power indicators show remaining battery capacity during battery charging and while being used to charge devices
- Features overcharge, over-discharge, output current and short circuit protections

Package Includes

- UPBW-05K0-1A1C
- Owner's Manual

Optional Accessories

- M100-Series USB-A to Lightning Cables
- U030-Series USB-A to USB Mini-B Cables
- UR05C-Series USB Micro-B Charge-Only Cables
- U038-Series USB-A to USB Type-C Cables

USB Device Charging

Notes:

- A button is located on the device next to the USB Type-C input port. When the button is pressed once, the device will turn on and the LED indicators will illuminate to show how much battery capacity is left.
 - When charging a USB device, the LED indicators on the device will illuminate in one of four combinations to indicate the following battery capacity levels:
 - 75-100% Capacity – 4 LEDs illuminate solid
 - 50-75% Capacity – 3 LEDs illuminate solid
 - 25-50% Capacity – 2 LEDs illuminate solid
 - 5-25% Capacity – 1 LED illuminates solid
 - 0-5% Capacity – 0 LEDs illuminate
 - When the Mobile Power Bank is plugged into an outlet, it starts charging devices attached to the two USB ports first and will charge the internal battery with the remaining power.
1. Connect up to two mobile devices to the USB-A or USB Type-C ports on the power bank using a cable suitable for your device.
Note: See **Optional Accessories** for compatible Tripp Lite USB device cables
 2. The device will begin charging with the LED indicator light(s) illuminating according to the combinations listed above.
 3. When charging the Mobile Power Bank in a wall outlet, the device's four LED lights will blink as it reaches each level of charging capacity.

General Safety Instructions

- When using the Mobile Power Bank as a portable charger, make sure it is fully charged prior to use.
- Use a cable suitable for your device when charging it from the Mobile Power Bank.
- When the battery is low, the LED lights will turn off while charging a device. Recharge the Mobile Power Bank as soon as possible to avoid shortening the battery life.
- It is recommended to disconnect a fully charged device to avoid unnecessary Mobile Power Bank battery use.
- Keep the Mobile Power Bank away from fire and avoid temperatures above 140°F (60°C) when not in use or 113°F (45°C) when in use.
- Do not get the Mobile Power Bank wet or immerse it in water.
- Do not wash the Mobile Power Bank with corrosive cleaner.
- Do not squeeze or puncture the Mobile Power Bank so as to avoid electrolyte leakage of lithium-ion battery.
- Do not attempt to disassemble, modify or fix the Mobile Power Bank.
- Do not use a damaged cable or power charger to charge the Mobile Power Bank.
- Please recycle this device at an appointed disposal location for lithium-ion batteries.

Specifications

Input (AC)	110-240V, 50/60 Hz, 0.5A
Input (DC)	5V/3A (15W)
Output (Plugged into Outlet)	USB-C Port: 5V/2.4A USB-A Port: 5V/2.4A
Output (Mobile)	USB-C Port: 5V/3A USB-A Port: 5V/2.4A
Ripple and Noise	≤ 200mVp-p
Operating Temperature Range	32 ~ 77°F (0 ~ 25°C)
Storage Temperature Range	-4 ~ 140°F (-20 ~ 60°C)
Operating Humidity Range	20 ~ 90% RH
Storage Humidity Range	5 ~ 45% RH
Color	Black
Dimensions	1.18" x 2.72" x 3.07" (30 x 69 x 78 mm)
Over-Current Protection	Yes
Over-Voltage Protection	Yes
Over-Heating Protection	Yes
Short Circuit Protection	Yes
Efficiency	≥ 80 %

Warranty

1-Year Limited Warranty

TRIPP LITE warrants its products to be free from defects in materials and workmanship for a period of one (1) year from the date of initial purchase. TRIPP LITE's obligation under this warranty is limited to repairing or replacing (at its sole option) any such defective products. To obtain service under this warranty, you must obtain a Returned Material Authorization (RMA) number from TRIPP LITE or an authorized TRIPP LITE service center. Products must be returned to TRIPP LITE or an authorized TRIPP LITE service center with transportation charges prepaid and must be accompanied by a brief description of the problem encountered and proof of date and place of purchase. This warranty does not apply to equipment which has been damaged by accident, negligence or misapplication or has been altered or modified in any way.

EXCEPT AS PROVIDED HEREIN, TRIPP LITE MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Some states do not permit limitation or exclusion of implied warranties; therefore, the aforesaid limitation(s) or exclusion(s) may not apply to the purchaser.

EXCEPT AS PROVIDED ABOVE, IN NO EVENT WILL TRIPP LITE BE LIABLE FOR DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES ARISING OUT OF THE USE OF THIS PRODUCT, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE. Specifically, TRIPP LITE is not liable for any costs, such as lost profits or revenue, loss of equipment, loss of use of equipment, loss of software, loss of data, costs of substitutes, claims by third parties, or otherwise.

FCC Notice, Class B

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications.

Warranty and Product Registration

However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Any changes or modifications to this equipment not expressly approved by Tripp Lite could void the user's authority to operate this equipment.

PRODUCT REGISTRATION

Visit tripplite.com/warranty today to register your new Tripp Lite product. You'll be automatically entered into a drawing for a chance to win a FREE Tripp Lite product!*

* No purchase necessary. Void where prohibited. Some restrictions apply. See website for details.

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Manufacturing
Excellence.

1111 W. 35th Street, Chicago, IL 60609 USA • tripplite.com/support